



FL107A

Steel enclosure, Orion.Plus, plain door 400x300x200 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	200 mm
Internal depth	200 mm
Height of installed product	400 mm
Width of installed product	300 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of keys	1
Number of openings for flange plates	2
Extension possible	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
------------------	--------------

Fire resistance	-
-----------------	---