



FL110A

Steel enclosure, Orion.Plus, plain door 500x300x200 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	30
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	200 mm
----------------------------	--------

Internal depth	195 mm
----------------	--------

Height of installed product	500 mm
-----------------------------	--------

Width of installed product	300 mm
----------------------------	--------

Width in division units	10
-------------------------	----

Thickness of sidewall material	2 mm
--------------------------------	------

Cover, door

Material thickness cover	21.5 mm
--------------------------	---------

Interlockable	Yes
---------------	-----

Number of keylock of the door	1
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	No
---------------------------	----

Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Material	Steel
----------	-------

Type of surface treatment	powder-coated
---------------------------	---------------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	3
Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK10
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-