



FL110A

Steel enclosure, Orion.Plus, plain door 500x300x200 mm

Technical properties

Architecture

Fixing mode Wall mounting

Functions

Cover with overpressure release No

Configuration

Number of modules 30

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 200 mm

Internal depth 195 mm

Height of installed product 500 mm

Width of installed product 300 mm

Width in division units 10

Thickness of sidewall material 2 mm

Cover, door

Material thickness cover 21.5 mm

Type of door closing lock with male triangular wrench

Interlockable Yes

Number of keylock of the door 1

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

Type of surface treatment powder-coated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	3
Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK10
Protection index IP	IP65
Protection class	isol.class I
Fire resistance	-