



FL111A



## Steel enclosure, Orion.Plus, plain door 500x400x160 mm

### Technical properties

#### Functions

Cover with overpressure release	No
---------------------------------	----

#### Configuration

Number of modules	54
-------------------	----

#### Compatibility

Suitable for lightning protection	No
-----------------------------------	----

#### Electric current

Rated current	630 A
---------------	-------

#### Dimensions

Depth of installed product	160 mm
----------------------------	--------

Internal depth	160 mm
----------------	--------

Height of installed product	500 mm
-----------------------------	--------

Width of installed product	400 mm
----------------------------	--------

Width in division units	16
-------------------------	----

Thickness of sidewall material	1.2 mm
--------------------------------	--------

#### Cover, door

Material thickness cover	1.5 mm
--------------------------	--------

Interlockable	Yes
---------------	-----

Cover type	Closed (plain)
------------	----------------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	No
---------------------------	----

#### Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Type of surface treatment	powder-coated
---------------------------	---------------

#### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

#### Settings

Enclosure type	Wall cabinet
----------------	--------------

#### Equipment

Number of rows	3
----------------	---

Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

### Standards

European directive WEEE	not concerned
-------------------------	---------------

### Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-