



FL118A

**Steel enclosure, Orion.Plus, plain door 650x400x250 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	72
-------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Depth of installed product	250 mm
Internal depth	245 mm
Height of installed product	650 mm
Width of installed product	400 mm
Width in division units	16
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	1.2 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Subject to technical modifications

Number of rows	4
Quantity of section in width	0
Number of keys	2
Number of openings for flange plates	2
Extension possible	Yes

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-