



FL123A

**Steel enclosure, Orion.Plus, plain door 800x600x250 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	130
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	250 mm
Depth of installed product	250 mm
Internal depth	250 mm
Height of installed product	800 mm
Width of installed product	600 mm
Width in division units	26
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	2 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Transparent cover or door	No

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Subject to technical modifications

Number of rows	5
Number of keys	2
Number of openings for flange plates	2
Extension possible	Yes
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-