



FL152A



Steel enclosure, Orion.Plus, glazed door 300x250x160 mm

Technical properties

Functions

Cover with overpressure release No

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 300 mm

Width of installed product 250 mm

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 1.5 mm

Interlockable Yes

Number of keylock of the door 1

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Wall cabinet

Equipment

Number of keys 1

Number of openings for flange plates 2

Extension possible Yes

Standards

European directive WEEE

not concerned

Safety

IK protection code against mechanical impacts

IK10

Protection class

isol.class I

REACH conform

No

RoHS conform

Yes

Halogen free

No

Fire resistance

-