



FL153A



**Steel enclosure, Orion.Plus, glazed door 300x300x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 160 mm

Internal depth 155 mm

Height of installed product 300 mm

Width of installed product 300 mm

Thickness of sidewall material 2 mm

**Cover, door**

Material thickness cover 21.5 mm

Interlockable Yes

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of keys 1

Number of openings for flange plates 2

Extension possible Yes

**Standards**

**Safety**

---

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-