



FL153A

Steel enclosure, Orion.Plus, glazed door 300x300x160 mm

Technical properties

Functions

Cover with overpressure release No

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 160 mm

Internal depth 155 mm

Height of installed product 300 mm

Width of installed product 300 mm

Thickness of sidewall material 2 mm

Cover, door

Material thickness cover 21.5 mm

Type of door closing lock with male triangular wrench

Interlockable Yes

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Wall cabinet

Equipment

Number of keys 1

Number of openings for flange plates 2

Extension possible Yes

Subject to technical modifications

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
------------------	--------------

Fire resistance	-
-----------------	---