



FL154A

**Steel enclosure, Orion.Plus, glazed door 350x300x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 20

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 350 mm

Width of installed product 300 mm

Width in division units 10

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 21.5 mm

Type of door closing lock with male triangular wrench

Interlockable Yes

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows	2
Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection class	isol.class I
Fire resistance	-