



FL154A

Steel enclosure, Orion.Plus, glazed door 350x300x160 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	20
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	350 mm
Width of installed product	300 mm
Width in division units	10
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	21.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	2
----------------	---

Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	not concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-