



FL156A

**Steel enclosure, Orion.Plus, glazed door 400x300x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	400 mm
Width of installed product	300 mm
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	1.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Settings**

Enclosure type	Wall cabinet
----------------	--------------

**Equipment**

Number of keys	1
Number of openings for flange plates	2
Extension possible	No

**Standards**

---

European directive WEEE not concerned

**Safety**

---

Protection class isol.class I

---

Fire resistance -