



FL156A



Steel enclosure, Orion.Plus, glazed door 400x300x160 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	400 mm
Width of installed product	300 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	1.5 mm
Interlockable	Yes
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of keys	1
Number of openings for flange plates	2
Extension possible	No

Standards

Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-