



FL160A

**Steel enclosure, Orion.Plus, glazed door 500x300x200 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 30

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 200 mm

Internal depth 195 mm

Height of installed product 500 mm

Width of installed product 300 mm

Width in division units 10

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 21.5 mm

Interlockable Yes

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows 3

Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

### Standards

European directive WEEE	not concerned
-------------------------	---------------

### Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-