



FL162A

Steel enclosure, Orion.Plus, glazed door 500x400x100 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	48
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	200 mm
Depth of installed product	200 mm
Internal depth	100 mm
Height of installed product	500 mm
Width of installed product	400 mm
Width in division units	16
Thickness of sidewall material	1.2 mm

Cover, door

Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	3
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
Fire resistance	-