



FL163A

Steel enclosure, Orion.Plus, glazed door 500x500x200 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	100 mm
Depth of installed product	200 mm
Internal depth	300 mm
Height of installed product	500 mm
Width of installed product	500 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of keys	1
Number of openings for flange plates	2
Extension possible	No

Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-