



FL167A



Steel enclosure, Orion.Plus, glazed door 650x400x200 mm

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 64

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 200 mm

Depth of installed product 200 mm

Internal depth 200 mm

Height of installed product 650 mm

Width of installed product 400 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 21.5 mm

Interlockable Yes

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use Yes

Settings

Enclosure type Wall cabinet

Equipment

Number of rows	4
Quantity of section in width	0
Number of keys	2
Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	not concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-