



FL177A

Steel enclosure, Orion.Plus, glazed door 950x800x250 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	222
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	250 mm
Depth of installed product	250 mm
Internal depth	250 mm
Height of installed product	950 mm
Width of installed product	800 mm
Width in division units	37
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Subject to technical modifications

Enclosure type

Wall cabinet

Equipment

Number of rows

6

Number of keys

2

Number of openings for flange plates

2

Extension possible

Yes

Standards

European directive WEEE

not concerned

Safety

Protection class

isol.class I

Fire resistance

-