



FL204B

Polyester enclosure, Orion.Plus, plain door 350x300x160 mm

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 24

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 350 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 2 mm

Cover, door

Interlockable Yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use Yes

Settings

Enclosure type Wall cabinet

Equipment

Number of rows 2

Number of keys	2
Quantity of rails	2
Number of openings for flange plates	0

Standards

Approvals	BS EN 62208
-----------	-------------

Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes