



FL216B

**Polyester enclosure, Orion.Plus, plain door 650x400x200 mm**

**Technical properties**

**Functions**

|                                 |    |
|---------------------------------|----|
| Cover with overpressure release | No |
|---------------------------------|----|

**Configuration**

|                   |    |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

**Compatibility**

|                                   |    |
|-----------------------------------|----|
| Suitable for lightning protection | No |
|-----------------------------------|----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

**Dimensions**

|                                |        |
|--------------------------------|--------|
| Depth of installed product     | 200 mm |
| Internal depth                 | 200 mm |
| Height of installed product    | 650 mm |
| Width of installed product     | 400 mm |
| Width in division units        | 18     |
| Thickness of sidewall material | 2 mm   |

**Cover, door**

|                               |                |
|-------------------------------|----------------|
| Interlockable                 | Yes            |
| Number of keylock of the door | 2              |
| Cover type                    | Closed (plain) |
| Door leave                    | single         |
| Cover type                    | Door           |
| Transparent cover or door     | No             |

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | light grey            |
| RAL colour                | RAL 7035 - Light grey |
| Type of surface treatment | untreated             |

**Installation, mounting**

|                          |     |
|--------------------------|-----|
| Suitable for outdoor use | Yes |
|--------------------------|-----|

**Settings**

|                |              |
|----------------|--------------|
| Enclosure type | Wall cabinet |
|----------------|--------------|

**Equipment**

|                |   |
|----------------|---|
| Number of rows | 4 |
|----------------|---|

|                                      |   |
|--------------------------------------|---|
| Number of keys                       | 2 |
| Quantity of rails                    | 4 |
| Number of openings for flange plates | 0 |

---

**Standards**

|           |             |
|-----------|-------------|
| Approvals | BS EN 62208 |
|-----------|-------------|

---

**Safety**

|   |               |
|---|---------------|
| IK protection code against mechanical impacts | IK10          |
| Protection class                              | isol.class II |
| REACH conform                                 | No            |
| RoHS conform                                  | Yes           |