



FL221B

**Polyester enclosure, Orion.Plus, plain door 650x500x250 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	96
-------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Depth of installed product	250 mm
Internal depth	250 mm
Height of installed product	650 mm
Width of installed product	500 mm
Width in division units	24
Thickness of sidewall material	2 mm

**Cover, door**

Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	Yes
--------------------------	-----

**Settings**

Enclosure type	Wall cabinet
----------------	--------------

**Equipment**

Number of rows	4
----------------	---

Number of keys	2
Quantity of rails	4
Number of openings for flange plates	0

---

**Standards**

Approvals	BS EN 62208
-----------	-------------

---

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes