



FL229B

**Polyester enclosure, Orion.Plus, plain door 800x600x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 140

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 800 mm

Width of installed product 600 mm

Width in division units 28

Thickness of sidewall material 2 mm

**Cover, door**

Interlockable Yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows 4

Number of keys	2
Quantity of rails	5
Number of openings for flange plates	0

---

**Standards**

Approvals	BS EN 62208
-----------	-------------

---

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes