



FL229B

Polyester enclosure, Orion.Plus, plain door 800x600x300 mm

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 140

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 800 mm

Width of installed product 600 mm

Width in division units 28

Thickness of sidewall material 2 mm

Cover, door

Type of door closing lock with male triangular wrench

Interlockable Yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reinforced polyester

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use Yes

Settings

Enclosure type Wall cabinet

Equipment

Number of rows	4
Number of keys	2
Quantity of rails	5
Number of openings for flange plates	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP66
Protection class	isol.class II
