



FL259B

Polyester enclosure, Orion.Plus, glazed door 500x300x200 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	36
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	200 mm
Internal depth	200 mm
Height of installed product	500 mm
Width of installed product	300 mm
Width in division units	12
Thickness of sidewall material	3 mm

Cover, door

Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reinforced polyester
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	3
----------------	---

Number of keys	2
Quantity of rails	3
Number of openings for flange plates	0

Standards

Approvals	BS EN 62208
European directive WEEE	not concerned

Safety

Protection index IP	IP66
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes