



FL279B

Polyester enclosure, Orion.Plus, glazed door 800x600x300 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	140
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	800 mm
Width of installed product	600 mm
Width in division units	28
Thickness of sidewall material	3 mm

Cover, door

Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	5
----------------	---

Number of keys	2
Quantity of rails	5
Number of openings for flange plates	0

Standards

Approvals	BS EN 62208
-----------	-------------

Safety

IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes