



FL301B

Polyester wall mounting enclosure, Orion.Plus, plain door 850x600x300 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	23
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	850 mm
Width of installed product	600 mm
Width in division units	23
Thickness of sidewall material	1.5 mm

Cover, door

Type of door closing	lock with male triangular wrench
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reeinforced polyester
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	5
Quantity of section in width	1

Subject to technical modifications

Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Fire resistance	-