



FL301B

**Polyester wall mounting enclosure, Orion.Plus, plain door 850x600x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 23

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 850 mm

Width of installed product 600 mm

Width in division units 23

Thickness of sidewall material 1.5 mm

**Cover, door**

Type of door closing lock with male triangular wrench

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reinforced polyester

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows	5
Quantity of section in width	1
Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes

---

**Standards**

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

Protection class	isol.class II
Fire resistance	-