



FL301B

**Polyester wall mounting enclosure, Orion.Plus, plain door 850x600x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 23

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 850 mm

Width of installed product 600 mm

Width in division units 23

Thickness of sidewall material 1.5 mm

**Cover, door**

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows 5

Quantity of section in width 1

Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes
<b>Safety</b>	
IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Fire resistance	-