



FL302B

**Polyester wall mounting enclosure, Orion.Plus, plain door 1150x600x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	161
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	1150 mm
Width of installed product	600 mm
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	2 mm
Type of door closing	Barrel lock
Interlockable	Yes
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reinforced polyester

**Installation, mounting**

Suitable for outdoor use	Yes
--------------------------	-----

**Settings**

Enclosure type	Wall cabinet
----------------	--------------

**Equipment**

Number of rows	7
Quantity of section in width	1
Number of keys	2
Number of openings for flange plates	0
Extension possible	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection class	isol.class II
Fire resistance	-