



FL306B

Polyester wall mounting enclosure, Orion.Plus, plain door 850x850x300 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	185
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	850 mm
Width of installed product	850 mm
Thickness of sidewall material	1.5 mm

Cover, door

Type of door closing	lock with male triangular wrench
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	plastic

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	5
----------------	---

Quantity of section in width	1
Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
Fire resistance	-