



FL311B

**Polyester wall mounting enclosure, Orion.Plus, plain door 850x1100x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 230

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 850 mm

Width of installed product 1100 mm

Thickness of sidewall material 1.5 mm

**Cover, door**

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows 5

Quantity of section in width 2

Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes

---

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

---

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
Fire resistance	-