



FL320B

Polyester floor standing enclosure, Orion.Plus, plain door 600x600x300 mm

Technical properties

Architecture

Fixing mode Floor fastening

Functions

Cover with overpressure release No

Configuration

Number of modules 69

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 200 mm

Height of installed product 600 mm

Width of installed product 600 mm

Thickness of sidewall material 1.5 mm

Cover, door

Type of door closing lock with male triangular wrench

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use Yes

Settings

Equipment

Number of rows	3
Quantity of section in width	1
Number of keys	1
Number of openings for flange plates	0
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK10
Protection index IP	IP65
Protection class	isol.class II
REACH conform	No
Fire resistance	-