



FL325B

**Polyester floor standing enclosure, Orion.Plus, plain door 600x850x300 mm**

**Technical properties**

**Architecture**

Fixing mode Floor fastening

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 111

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 600 mm

Width of installed product 850 mm

Thickness of sidewall material 1.5 mm

**Cover, door**

Type of door closing lock with male triangular wrench

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

**Equipment**

Number of rows	3
Quantity of section in width	1
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	IK10
Protection index IP	IP65
Protection class	isol.class II
REACH conform	No
Fire resistance	-