



FL327B

Polyester floor standing enclosure, Orion.Plus, plain door 1200x850x300 mm

Technical properties

Architecture

Fixing mode Wall mounting

Functions

Cover with overpressure release No

Configuration

Number of modules 259

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 1200 mm

Width of installed product 850 mm

Thickness of sidewall material 2 mm

Cover, door

Type of door closing Barrel lock

Interlockable Yes

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reinforced polyester

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use Yes

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	7
Quantity of section in width	1
Number of keys	2
Number of openings for flange plates	0
Extension possible	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK08
Protection index IP	IP65
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Fire resistance	-