



FL348B

Polyester double enclosure, Orion.Plus, plain door 2050x600x300 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	115
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	2050 mm
Width of installed product	600 mm
Thickness of sidewall material	1.5 mm

Cover, door

Type of door closing	lock with male triangular wrench
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	3
Quantity of section in width	1
Number of keys	2

Subject to technical modifications

Number of openings for flange plates	0
Extension possible	Yes
Standards	
European directive WEEE	not concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
Fire resistance	-