



FL352B

Polyester double enclosure, Orion.Plus, plain door 1450x850x300 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	111
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	1450 mm
Width of installed product	850 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	2 mm
Interlockable	Yes
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	3
----------------	---

Quantity of section in width	1
Number of keys	2
Number of openings for flange plates	0
Extension possible	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Fire resistance	-