



FL412A

Steel mounting plate, Orion.Plus, 630x343 mm

Technical properties

Dimensions

Depth of installed product	2 mm
Height of installed product	630 mm
Width of installed product	343 mm

Materials

Colour	metallic
Material	Steel
Type of surface treatment	Sendzimir galvanized

Standards

Approvals	CE
European directive WEEE	not concerned

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes