



FL424A

**Insulated mounting plate, Orion.Plus, 435x245 mm**

**Technical properties**

**Dimensions**

Depth of installed product	4 mm
Height of installed product	435 mm
Width of installed product	245 mm

**Materials**

Type of surface treatment	untreated
---------------------------	-----------

**Standards**

Approvals	CE
European directive WEEE	not concerned

**Safety**

REACH conform	Yes
RoHS conform	Yes