



FL502B

**Polyester wall mounting enclosure, Orion.Plus, 1150x600x300 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	161
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	1150 mm
Width of installed product	600 mm
Thickness of sidewall material	1.5 mm

**Cover, door**

Type of door closing	lock with male triangular wrench
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	Yes

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	Yes
--------------------------	-----

**Equipment**

Number of rows	7
Number of keys	2
Number of openings for flange plates	0

Extension possible	Yes
<b>Standards</b>	
European directive WEEE	not concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
Protection class	isol.class II
REACH conform	No
Fire resistance	-