



FL544A

Steel inner door, Orion.Plus steel, 350x300 mm

Technical properties

Architecture

Fixing mode	Screw mounting
-------------	----------------

Dimensions

Depth of installed product	20 mm
Height of installed product	300 mm
Width of installed product	250 mm

Cover, door

Type of door closing	Double lock bar 3mm
----------------------	---------------------

Materials

Colour	RAL 7035
Colour	zinc optics
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	untreated

Equipment

Number of keys	1
----------------	---

Standards

Approvals	CE
European directive WEEE	not concerned

Safety

Protection index IP	IP30
Protection class	isol.class I
REACH conform	No