



FL544A

Steel inner door, Orion.Plus steel, 350x300 mm

Technical properties

Dimensions

Depth of installed product	20 mm
Height of installed product	300 mm
Width of installed product	250 mm

Materials

RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Equipment

Number of keys	1
----------------	---

Standards

Approvals	CE
European directive WEEE	not concerned

Safety

Protection class	isol.class I
REACH conform	No