



FL547A

Steel inner door, Orion.Plus steel, 500x300 mm

Technical properties

Architecture

Fixing mode Screw mounting

Dimensions

Depth of installed product 20 mm

Height of installed product 450 mm

Width of installed product 250 mm

Cover, door

Type of door closing Double lock bar 3mm

Door type for switch gear cabinet Inner door

Materials

Colour RAL 7035

Colour zinc optics

RAL colour RAL 7035 - Light grey

Material Steel

Type of surface treatment untreated

Equipment

Number of keys 2

Standards

European directive WEEE not concerned

Safety

Protection index IP IP30

Protection class isol.class I