



FL551A

**Steel inner door, Orion.Plus steel, 650x400 mm**

**Technical properties**

**Architecture**

Fixing mode Screw mounting

**Dimensions**

Depth of installed product 20 mm

Height of installed product 600 mm

Width of installed product 350 mm

**Cover, door**

Type of door closing Double lock bar 3mm

Door type for switch gear cabinet Inner door

**Materials**

Colour RAL 7035

Colour zinc optics

RAL colour RAL 7035 - Light grey

Material Steel

Type of surface treatment untreated

**Equipment**

Number of keys 2

**Standards**

European directive WEEE not concerned

**Safety**

Protection index IP IP30

Protection class isol.class I