



FL558A

Steel counterdoor, Orion.Plus sheet metal, H1250 W600 mm

Technical properties

Dimensions

Depth of installed product	20 mm
Height of installed product	1200 mm
Width of installed product	550 mm

Cover, door

Type of door closing	Double lock bar 3mm
Door type for switch gear cabinet	Lock door
Transparent cover or door	No

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

Equipment

Number of keys	2
----------------	---

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP65
---------------------	------