



FL602E

**Steel inner door, Orion.Plus, H1050 W750 mm**

**Technical properties**

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 20 mm   |
| Height of installed product | 1050 mm |
| Width of installed product  | 750 mm  |

**Cover, door**

|                           |    |
|---------------------------|----|
| Transparent cover or door | No |
|---------------------------|----|

**Materials**

|            |                       |
|------------|-----------------------|
| Colour     | light grey            |
| RAL colour | RAL 7035 - Light grey |

**Equipment**

|                |   |
|----------------|---|
| Number of keys | 2 |
|----------------|---|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|                  |              |
|------------------|--------------|
| Protection class | isol.class I |
| REACH conform    | No           |