



FL644A

**Polyester inner door, Orion.Plus polyester, 500x300 mm**

**Technical properties**

**Architecture**

|             |                |
|-------------|----------------|
| Fixing mode | Screw mounting |
|-------------|----------------|

**Dimensions**

|                             |        |
|-----------------------------|--------|
| Depth of installed product  | 20 mm  |
| Height of installed product | 450 mm |
| Width of installed product  | 250 mm |

**Cover, door**

|                                   |                     |
|-----------------------------------|---------------------|
| Type of door closing              | Double lock bar 3mm |
| Door type for switch gear cabinet | Inner door          |

**Materials**

|                           |                            |
|---------------------------|----------------------------|
| Colour                    | RAL 7035                   |
| Colour                    | light grey                 |
| RAL colour                | RAL 7035 - Light grey      |
| Material                  | glas reeinforced polyester |
| Surface appearance        | matt                       |
| Type of surface treatment | untreated                  |

**Equipment**

|                |   |
|----------------|---|
| Number of keys | 2 |
|----------------|---|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|                     |               |
|---------------------|---------------|
| Protection index IP | IP30          |
| Protection class    | isol.class II |