



FL645A

**Polyester inner door, Orion.Plus polyester, 500x400 mm**

**Technical properties**

**Architecture**

Fixing mode	Screw mounting
-------------	----------------

**Dimensions**

Depth of installed product	20 mm
Height of installed product	450 mm
Width of installed product	350 mm

**Cover, door**

Type of door closing	Double lock bar 3mm
Door type for switch gear cabinet	Inner door

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reinforced polyester
Surface appearance	matt
Type of surface treatment	untreated

**Equipment**

Number of keys	2
----------------	---

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection index IP	IP30
Protection class	isol.class II