



FL647A

Polyester inner door, Orion.Plus polyester, 650x500 mm

Technical properties

Architecture

Fixing mode	Screw mounting
-------------	----------------

Dimensions

Depth of installed product	20 mm
Height of installed product	600 mm
Width of installed product	450 mm

Cover, door

Type of door closing	Double lock bar 3mm
Door type for switch gear cabinet	Inner door

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reeinforced polyester
Surface appearance	matt
Type of surface treatment	untreated

Equipment

Number of keys	2
----------------	---

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP30
Protection class	isol.class II