



FM108

Floor standing steel enclosure, Quadro5, 1860x400x260 mm

Technical properties

Configuration

Number of modules 110

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 260 mm

Depth of installed product 260 mm

Internal depth 260 mm

Height of installed product 1860 mm

Width of installed product 450 mm

Width in division units 10

Thickness of sidewall material 2 mm

Cover, door

Material thickness cover 2 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Equipment

Number of rows 12

Quantity of section in width 1

Number of openings for flange plates 2

Extension possible Yes

Standards

Subject to technical modifications

Safety

IK protection code against mechanical impacts	IK10
REACH conform	No
Fire resistance	-