



FM117

Floor standing steel enclosure, Quadro5, 1710x400x400 mm

Technical properties

Architecture

Fixing mode	Floor fastening
-------------	-----------------

Configuration

Number of modules	100
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	400 mm
Height of installed product	1710 mm
Width of installed product	450 mm
Width in division units	10
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Interlockable	No
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	metal
Type of surface treatment	Galvanised

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	11
----------------	----

Quantity of section in width	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK10
Protection index IP	IP55
Protection class	isol.class I
REACH conform	No
Fire resistance	-